


UL Fuses 5x20 5TT Slow Blow

Complying with UL / CSA 248-14

250 VAC / 125 VAC
FROM 0.08 TO 10 A

Dimensions

Glass tube \leq 5A. Ceramic tube \geq 6A



Max weight: 1.2 g



Basic Characteristics

Size mm	Rated Voltage VAC	Rated Current A	Breaking Capacity under		Max power dissip W	Max voltage drop V	Designation	Reference Number	Catalog Number
			250 VAC	125 VAC					
5 x 20	250	0,080*	100	10 000	0,45	2,8	250V 5TT 0,080 A 5 x 20	N207564	MI5TT 25V0,08
		0,100					250V 5TT 0,100 A 5 x 20	P207565	MI5TT 25V0,1
		0,125					250V 5TT 0,125 A 5 x 20	Q207566	MI5TT 25V0,125
		0,200					250V 5TT 0,200 A 5 x 20	R207567	MI5TT 25V0,2
		0,250					250V 5TT 0,250 A 5 x 20	S207568	MI5TT 25V0,25
		0,300					250V 5TT 0,300 A 5 x 20	T207569	MI5TT 25V0,3
		0,400					250V 5TT 0,400 A 5 x 20	V207570	MI5TT 25V0,4
		0,500					250V 5TT 0,500 A 5 x 20	W207571	MI5TT 25V0,5
		0,600					250V 5TT 0,600 A 5 x 20	X207572	MI5TT 25V0,6
		0,700					250V 5TT 0,700 A 5 x 20	Y207573	MI5TT 25V0,7
		0,750					250V 5TT 0,750 A 5 x 20	Z207574	MI5TT 25V0,75
		0,800					250V 5TT 0,800 A 5 x 20	A207575	MI5TT 25V0,8
		1,000					250V 5TT 1 A 5 x 20	B207576	MI5TT 25V1
		1,250					250V 5TT 1,25 A 5 x 20	C207577	MI5TT 25V1,250
	1,500	250V 5TT 1,5 A 5 x 20	D207578	MI5TT 25V1,5					
	1,600	250V 5TT 1,6 A 5 x 20	E207579	MI5TT 25V1,6					
	2,000	250V 5TT 2 A 5 x 20	F207580	MI5TT 25V2					
	2,500	250V 5TT 2,5 A 5 x 20	G207581	MI5TT 25V2,5					
	3,000	250V 5TT 3 A 5 x 20	H207582	MI5TT 25V3					
	125	4,000	1,25	125V 5TT 4 A 5 x 20	J207606	MI5TT 12,5V4			
5,000		1,33	125V 5TT 5 A 5 x 20	K207607	MI5TT 12,5V5				
6,000		1,23	125V 5TT 6 A 5 x 20	L207608	MI5TT 12,5V6				
7,000		—	125V 5TT 7 A 5 x 20	M207609	MI5TT 12,5V7				
8,000		—	125V 5TT 8 A 5 x 20	N207610	MI5TT 12,5V8				
10,000		—	125V 5TT 10 A 5 x 20	F208937	MI5TT 12,5V10				

* Non approval rating


Miniature Fuses

UL Fuses 5x20 5TT Slow Blow

Melting time limits

Current	100 % x In	135 % x In	200 % x In	
0,08 -> 3 A	4 h mini	1 h maxi	5s mini	30s maxi
4 A -> 10 A	4h mini	1 h maxi	3s mini	30s maxi

Time-current characteristics



Packaging: in box of 1000 pieces.
in blister of 50 pieces.